



Powering Business Worldwide

pe.eaton.com

E57 Series Tubular Metal Faced Inductive Proximity Sensor

41-3261

UPC:782113967967

Dimensions:

- **Height:** 2.68 IN
- **Length:** .47 IN
- **Width:** .47 IN

Weight:.0625 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 100 mA at 30 Vdc
- **Contact Configuration:** Normally Open PNP
Open Collector
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12
and 13 (IP67)
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to
70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eaton Specification Sheet - 41-3261](#)

Certifications:

- UL Listed
- CSA Certified



Product compliance:

- CE Marked
- Contact Manufacturer

© 2016 Eaton. All rights reserved.