



Powering Business Worldwide

pe.eaton.com

General-Purpose Encapsulated Transformer

S20N11E07A

UPC:786680104664

Dimensions:

- **Height:** 16 IN
- **Length:** 9.89 IN
- **Width:** 10.38 IN

Weight:126 LB

Notes:Model A

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Electrostatically shielded
- **Type:** General-Purpose Encapsulated Transformer
- **Design:** EP
- **Coil Material:** Aluminum windings
- **Enclosure:** NEMA 3R
- **Frame:** 178
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 240 X 480V
- **Secondary Voltage:** 120/240V
- **Tap Size:** NONE
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 7.5 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 90A

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)



- [Eaton Specification Sheet - S20N11E07A](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.