



Powering Business Worldwide

pe.eaton.com

Enhanced 50 Series Photoelectric Sensor

1350E-6517

UPC:782116111435

Dimensions:

- **Height:** 3.46 IN
- **Length:** 1.91 IN
- **Width:** 1.81 IN

Weight: .5375 LB

Warranties:

- 3 year

Specifications:

- **Connection:** 6.6 Ft. (2m) Cable
- **Contact Rating:** 250 mA at 40 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NPN and PNP Open Collector
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Fiberglass reinforced plastic
- **Environmental Rating:** IP 67, IP69K
- **Input Voltage:** 10-40 Vdc
- **Led Indicators:** Yellow power on, Green outout status, red marginal gain
- **Maximum Dc Current:** 250 mA
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** Reverse polarity, short circuit and overload
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 1350E-6517](#)



Certifications: No Data

Product compliance:

- Contact Manufacturer

© 2016 Eaton. All rights reserved.