



Powering Business Worldwide

pe.eaton.com

E10 Series Light Industrial Toggle Switch

E10P115RP

UPC:782113699899

Dimensions:

- **Height:** 1.25 IN
- **Length:** .75 IN
- **Width:** 1.6 IN

Weight:.07 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Pushbutton Actuator
- **Bushing Length:** 0.69 inch bushing
- **Button Extension:** 0.53 inch button extension
- **Max Op Force:** 0.9 lbs
- **Number Of Poles:** Single-pole
- **Operating Mode:** Momentary
- **Rating:** 15A at 125 Vac (NO), 10A at 250 Vac (NO), 1/3 hp at 125-250 Vac
- **Series:** E10
- **Terminals:** Spade
- **Throw Type:** Single-throw

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - E10P115RP](#)

Certifications:

- UL Recognized
- CSA Certified



Product compliance: No Data

© 2016 Eaton. All rights reserved.