



Powering Business Worldwide

pe.eaton.com

Type LA Tri-Pac Thermal-Magnetic Circuit Breaker

LA3225PT

UPC:786679766163

Dimensions:

- **Height:** 5.1 IN
- **Length:** 10.1 IN
- **Width:** 5.3 IN

Weight:3 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Trip unit only
- **Amperage Rating:** 225A
- **Interrupt Rating:** 200 kAIC at 600 Vac, 100 kAIC at 250 Vdc
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600 Vac, 250 Vdc
- **Magnetic Trip Range:** 1125-2250A
- **Terminals:** Without

Supporting documents:

- [Miniature and Molded Case Circuit Breakers](#)
- [Eaton Specification Sheet - LA3225PT](#)

Certifications:

- UL 489

Product compliance: No Data

