



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Molded Case Circuit Breakers Replacement Products

2606D56G19

UPC:786679935491

### Dimensions:

- Height: X
- Length: X
- Width: X

**Notes:** 120V suitable for 55% pickup for ground fault applications. Not field mountable on non-automatic breakers/molded case switches. Field mounting voids UL listing except on LA,HLA,MA,HMA,NB,HNB,PB,KB,HKB,KA,HKA,LB,HLB and SELTRONIC breakers.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Field mounting shunt trip
- **Voltage Rating:** 120V
- **Frequency Rating:** 50-60 Hz
- **Mounting:** Right-hand
- **Used With:** LA, LAB, HLA breaker

### Supporting documents:

- [E2 Mining Series Sales Brochure](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - 2606D56G19](#)

### Certifications:

- UL Listed

**Product compliance:** No Data



