



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Premium+ Inductive Proximity Sensor

**E57SAL18A2SA**

**UPC:**782113698069

### Dimensions:

- **Height:** .71 IN
- **Length:** 2.72 IN
- **Width:** .71 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Premium+ Inductive Proximity Sensor
- **Accuracy:** <1% sensing range
- **Connection:** Dual key micro
- **Contact Rating:** 250 mA at 40-240 Vac/20-250 Vdc
- **Contact Configuration:** 2-wire AC/DC, NO
- **Diameter:** .708661422 MM
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 40-250 Vac 50/60 Hz, 20-250 Vdc
- **Led Indicators:** 360° viewable LED
- **Maximum Ac Current:** 250 mA
- **Number Of Pins:** 3 pin
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Resettable S/C, overload
- **Series:** E57

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57SAL18A2SA](#)



**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.