



Powering Business Worldwide

pe.eaton.com

E50 Heavy Duty Plug-In Limit Switch

E50BS3

UPC:782113328485

Dimensions:

- **Height:** 4.22 IN
- **Length:** 1.54 IN
- **Width:** 2.94 IN

Weight:1.1063 LB

Notes:Roller can be converted in the field between horizontal and vertical

Warranties:

- 1 year

Specifications:

- **Accuracy:** Within 0.003
- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 240Vac, 1A at 250Vdc
- **Contact Configuration:** 2NO-2NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Switch Type:** Side Push Roller

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50BS3](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:



- CE Marked

© 2016 Eaton. All rights reserved.