



Powering Business Worldwide

pe.eaton.com

Prism Series Tubular Photoelectric Sensor

14151AS5300

UPC:782114023693

Dimensions:

- **Height:** 2.75 IN
- **Length:** .47 IN
- **Width:** .71 IN

Weight:.8875 LB

Warranties:

- 3 year

Specifications:

- **Connection:** 12 Ft. (3.7m) Shielded Cable
- **Contact Rating:** 110 mA at 30 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NPN Open Collector
- **Cord Length:** 144 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: Polycarbonate
Cable Jacket: PVC Body: Structural
Polyurethane Foam
- **Environmental Rating:** NEMA
1,3,4,4X,6,6P,12,13
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 110 mA
- **Operating Mode:** Polarized Retroreflective
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** Current Limited for loads less than
32V AC or DC
- **Switch Type:** Photoelectric

Supporting documents:

- [Eaton Specification Sheet - 14151AS5300](#)



Certifications: No Data

Product compliance:

- Contact Manufacturer

© 2016 Eaton. All rights reserved.