



Powering Business Worldwide

pe.eaton.com

Type Visi-Flex Disconnect Switch Component - Switch Only

2607D63G06

UPC:786679612460

Dimensions:

- **Height:** 6.3 IN
- **Length:** 7.5 IN
- **Width:** 6.2 IN

Weight:3.85 LB

Notes:External operating handle, shaft and no-fuse kit required. Rated 600 volts. Special 60Aere switch has same dimension as 30Aere Visi-Flex switch.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Disconnect switch
- **Amperage Rating:** 60A
- **Fuse Configuration:** Non-fusible
- **Max Hp Rating:** 7-1/2 hp at 120 Vac, 20 hp at 240 Vac, 40 hp at 480 Vac, 50 hp at 600 Vac, 10 hp at 250 Vdc
- **Switch Type:** Visi-Flex DE-ION
- **Trip Type:** Model A trip
- **Wire Size:** #14-#4 Cu

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - 2607D63G06](#)

Certifications:

- UL Listed



Product compliance: No Data

© 2016 Eaton. All rights reserved.