



Powering Business Worldwide

pe.eaton.com

Comet Series Tubular Photoelectric Sensor

11100AQD07

UPC:782113843407

Dimensions:

- **Height:** 2.2 IN
- **Length:** .47 IN
- **Width:** .71 IN

Weight:.1313 LB

Notes:For complete system; order 1 source and 1 detector. 11100 sources and 12100 detectors may be interchanged in any combination. The effective beam (minimum object size that can be detected) is 0.25 inch (6.5 mm) diameter.

Warranties:

- 3 year

Specifications:

- **Cable Type:** PVC
- **Cord Length:** 8 IN
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: Polycarbonate
Cable Jacket: PVC Body: Structural Polyurethane Foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red power on
- **Operating Mode:** Thru-beam
- **Operating Temperature:** -4° to 158°F (-20° to 70°C)
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

Supporting documents:

- [Comet series - Photoelectric sensors](#)



- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 11100AQD07](#)

Certifications:

- UL Recognized
- cUL Recognized

Product compliance:

- CE Marked
- Contact Manufacturer

© 2016 Eaton. All rights reserved.