



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Assembled Control Station

10250T3520

UPC:782113227160

Dimensions:

- **Height:** 3 IN
- **Length:** 6 IN
- **Width:** 3 IN

Weight: 1 LB

Notes: Lock is 10250TA2

Warranties:

- 1 year

Specifications:

- **Special Features:** With lock hasp
- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Pushbutton
- **Actuator Color:** Red
- **Contact Configuration:** 1NC
- **Enclosure Material:** Die cast
- **Legend:** STOP
- **Mounting:** Surface
- **Number Of Elements:** 1
- **Operating Mode:** Momentary
- **Rating:** NEMA 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T3520](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:



- CE Marked

© 2016 Eaton. All rights reserved.