



Powering Business Worldwide

pe.eaton.com

CN35 or A202 Enclosed Lighting Contactor

ECL03C2H3A

UPC:782114274262

Dimensions:

- **Height:** 14.188 IN
- **Length:** 11 IN
- **Width:** 8.5 IN

Weight:18 LB

Notes:Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 30A
- **Coil Voltage:** 277V/60 Hz
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted steel
- **Frame Size:** 45 mm
- **Number Of Poles:** Three-pole
- **Type:** Non-combination electrically held

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECL03C2H3A](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data

