



Powering Business Worldwide

pe.eaton.com

E65 Miniature Series Rectangular Body Photoelectric Sensor

E65LNL9FES

UPC:782113816203

Dimensions:

- **Height:** 3.35 IN
- **Length:** 2.4 IN
- **Width:** 1.7 IN

Weight:.58 LB

Warranties:

- 3 year

Specifications:

- **Connection:** 1.5 Ft. (0.5m) Cable
- **Contact Rating:** 100 mA at 40Vdc
- **Contact Configuration:** NPN Open Collector
- **Cord Length:** 19.2 FT
- **Enclosure Material:** Plastic
- **Environmental Rating:** NEMA 1,3,4,12,13, IP66
- **Input Voltage:** 10-31 Vdc
- **Led Indicators:** Red for OUT1, Yellow for OUT2
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Long Range Diffuse
- **Operating Temperature:** 5° to 131°F (-15° to 55°C)
- **Protection:** Short circuit
- **Sensor Type:** Diffuse Reflective
- **Switch Type:** Photoelectric

Supporting documents:

- [Eaton Specification Sheet - E65LNL9FES](#)

Certifications: No Data



Product compliance: No Data

© 2016 Eaton. All rights reserved.