



Powering Business Worldwide

pe.eaton.com

Adjustable Frequency Drive

SPX300A0-4A2N1

UPC:782116097371

Dimensions:

- **Height:** 45.9 IN
- **Length:** 19.9 IN
- **Width:** 19.7 IN

Weight:518 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** No brake chopper
- **Input:** Three-phase, EMC N
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR10
- **Horsepower:** 300 hp
- **Software:** Standard Software
- **Voltage Rating:** 480V

Supporting documents:

- [Eaton's Volume 6-Solid-State Motor Control](#)
- [SPX_\(FR10\) 3D Inventor](#)
- [Product Datasheet - SPX300A0-4A2N1](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - SPX300A0-4A2N1](#)
- [SPX_\(FR10\) AutoCAD 2D Footprint](#)
- [SPX_\(FR10\) AutoCAD 2D Footprint \(mm\)](#)
- [SPX_\(FR10\) 2D Drawing Xchange](#)
- [SPX_\(FR10\) 2D PDF](#)
- [SPX_\(FR10\) 3D Model Xchange](#)

Certifications:

- UL 508C



- EN 61800-3 Level H
- IEC 61800-2
- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.