



Powering Business Worldwide

pe.eaton.com

Meter Breaker Commercial Safety Sockets

CH227MTBLB

UPC:782116164950

Dimensions:

- **Height:** 44.44 IN
- **Length:** 6.06 IN
- **Width:** 12 IN

Notes: Order Type CC breaker or CCH breaker separately.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 200A
- **Feed Type:** Overhead
- **Number Of Jaws:** Seven-jaw
- **Phase:** Three-phase
- **Interrupt Rating:** Type CCV=10 kAIC, Type CCVH=25 kAIC
- **Main Circuit Breaker:** Provisions
- **Number Of Wires:** Four-wire
- **Security:** Ring
- **Used With:** Type CH breakers
- **Voltage Rating:** 208/108V
- **Wire Size:** #6-250 kcmil

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CH227MTBLB](#)

Certifications:

- UL Listed



Product compliance: No Data

© 2016 Eaton. All rights reserved.