



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## UNIPAK, Low Voltage Fixed Capacitor Banks

12043PMURF

UPC:782116058914

### Dimensions:

- **Height:** 26.3 IN
- **Length:** 10.6 IN
- **Width:** 12.1 IN

**Weight:**68.9 LB

**Notes:**Multiply the 240V kVAR rating by 0.75 to calculate the kVAR value at 208V.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** UNIPAK
- **Amperage Rating:** 144A
- **Enclosure:** NEMA 1, 3R
- **Enclosure Material:** 14 ga. steel finished w/durable powder coat finish
- **Frame Size:** C1
- **Fuse Type:** Three slottedblade type fuses with 200,000 ampere interrupting capacity, Fuses mounted on stand-off bushings or fuse blocks, solderless connectors for easy hookup of incoming line conductors.
- **Indicator:** Red, neon blown-fuse indicating lights are protected by transparent weatherproof guard
- **Phase:** Three-phase
- **Product Category:** Low Voltage Fixed Capacitor Banks



- **Protection:** Three fuses, three lights
- **Rating:** 120 kVAR
- **Voltage Rating:** 480V

**Supporting documents:**

- [Eatons Volume 3-Power Distribution and Control Assemblies](#)
- [Eaton Specification Sheet - 12043PMURF](#)

**Certifications:**

- UL Listed
- CSA Certified

**Product compliance:** No Data