



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Freedom Series IEC Contactor

**CE15JNS3BB**

**UPC:**782113035246

### Dimensions:

- **Height:** 4.27 IN
- **Length:** 4.22 IN
- **Width:** 2.56 IN

**Weight:**2.12 LB

**Notes:**No enclosure. For replacement only.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 60A
- **Coil Voltage:** 220/240V
- **Contact Configuration:** 1NO
- **Frame Size:** J-frame
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 10 hp
- **Mounting:** Steel mounting plate, Side mounted auxiliary contacts
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Relay:** No overload relay
- **Series:** Freedom
- **Type:** Contactor

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Drawing Link](#)
- [Eaton Specification Sheet - CE15JNS3BB](#)

### Certifications:

- UL Listed



- CSA Certified
- IEC Rated

**Product compliance:**

- DIN VDE 0600
- ISO 9000

---

© 2016 Eaton. All rights reserved.