



Powering Business Worldwide

pe.eaton.com

Inductive Global Proximity Sensor

E57-18GU08-A

UPC:782114289020

Dimensions:

- **Height:** .71 IN
- **Length:** 3.15 IN
- **Width:** .71 IN

Weight:.62 LB

Warranties:

- 1 year

Specifications:

- **Type:** E57
- **Accuracy:** <3.0% sensing range
- **Contact Rating:** 200 mA at 250V
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire AC, NO
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Nickel plated brass
- **Environmental Rating:** IP67, IP69K
- **Input Voltage:** 20-250V
- **Led Indicators:** Output ON
- **Maximum Ac Current:** 200 mA
- **Operating Mode:** Unshielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Temperature Rating:** -13° to 158°F

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Global Series inductive proximity sensors](#)
- [Eaton Specification Sheet - E57-18GU08-A](#)

Certifications: No Data

Product compliance: No Data



