



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General-Purpose Transformer, Ventilated

**T20P11B50**

**UPC:**786680023491

### Dimensions:

- **Height:** 42.03 IN
- **Length:** 23.84 IN
- **Width:** 24.22 IN

**Weight:**516 LB

**Notes:**+1 - 5% , -2 - 5% at 240V primary, +2 - 2.5%  
, -4 - 2.5% at 480V primary

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Dry Type Distribution Transformer
- **Design:** DS-3
- **Coil Material:** Aluminum windings
- **Frame:** 819
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 240 X 480V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 80°C
- **Volt Ampere Rating:** 50 KVA
- **Weathershield:** WS16

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - T20P11B50](#)

### Certifications:



- ANSI
- IEEE Certified

**Product compliance:**

- NEMA Compliant
- Meets UBC requirements
- California Code of Regulations

---

© 2016 Eaton. All rights reserved.