



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CN35 or A202 Enclosed Lighting Contactor

**ECL04C1B6A**

**UPC:**782114041628

### Dimensions:

- **Height:** 15.875 IN
- **Length:** 14.625 IN
- **Width:** 8.375 IN

**Weight:**15.5 LB

**Notes:**When using three-position selector switch, mod C20 must also be used (ECL04, ECL13, ECL15). Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 30A
- **Coil Voltage:** 220V/50 Hz, 240V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 45 mm
- **Number Of Poles:** Six-pole
- **Type:** Non-combination mechanically held and magnetically latched

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECL04C1B6A](#)

### Certifications:

- UL Listed
- cUL Listed

**Product compliance:** No Data



