



Powering Business Worldwide

pe.eaton.com

Inductive Global Proximity Sensor

E57-18GS05-DDB

UPC:782114665060

Dimensions:

- **Height:** .71 IN
- **Length:** 2.99 IN
- **Width:** .71 IN

Weight:.5 LB

Warranties:

- 1 year

Specifications:

- **Type:** E57
- **Accuracy:** <2.0% sensing range
- **Connection:** M12
- **Contact Rating:** 100 mA at 10-30 Vdc
- **Contact Configuration:** 2-wire DC, NO
- **Enclosure Material:** Nickel plated brass
- **Environmental Rating:** IP67, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Maximum Dc Current:** 100 mA
- **Number Of Pins:** 4 pin
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** S/C
- **Temperature Rating:** -13° to 158°F

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Global Series inductive proximity sensors](#)
- [Eaton Specification Sheet - E57-18GS05-DDB](#)

Certifications: No Data



Product compliance: No Data

© 2016 Eaton. All rights reserved.