



Powering Business Worldwide

pe.eaton.com

Meter Breaker Commercial Safety Sockets

CHU214MTBLB

UPC:782116164967

Dimensions:

- **Height:** 6 IN
- **Length:** 26 IN
- **Width:** 20 IN

Weight:65 LB

Notes:Order plug-on Type BR, BRH or BRHH circuit breaker separately.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 125A
- **Feed Type:** Underground
- **Interrupt Rating:** Type BR=10 kAIC, Type BRH=22 kAIC, Type BRHH=42 kAIC
- **Main Circuit Breaker:** Provisions
- **Number Of Jaws:** Four-jaw
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 240V
- **Wire Size:** #14-2/0 AWG

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHU214MTBLB](#)

Certifications:



- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.