



Powering Business Worldwide

pe.eaton.com

E57 Series Tubular Ferrous Only Inductive Proximity Sensor

E57FAL18A2B1

UPC:782113884639

Dimensions:

- **Height:** 3.9 IN
- **Length:** .71 IN
- **Width:** .71 IN

Weight:.14 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 3%
- **Connection:** 3 Pin Mini Connector
- **Contact Rating:** 100 mA at 250 Vac
- **Contact Configuration:** 2 - Wire AC, Normally Open
- **Diameter:** .71 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12 and 13 (IP67)
- **Input Voltage:** 20-250 Vac
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 100 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** None
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57FAL18A2B1](#)

Certifications:

- UL Listed



- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.