



Powering Business Worldwide

pe.eaton.com

Meter Breaker Commercial Safety Sockets

CH224MTBLB

UPC:782116164943

Dimensions:

- **Height:** 8 IN
- **Length:** 50 IN
- **Width:** 15 IN

Weight:50 LB

Notes:Order Type CC breaker or CCH breaker separately.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 200A
- **Feed Type:** Overhead
- **Number Of Jaws:** Four-jaw
- **Phase:** Single-phase
- **Interrupt Rating:** Type CCV=10 kAIC, Type CCVH=25 kAIC
- **Main Circuit Breaker:** Provisions
- **Number Of Wires:** Three-wire
- **Security:** Ring
- **Used With:** Type CH breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #6-250 kcmil

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CH224MTBLB](#)

Certifications:



- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.