



Powering Business Worldwide

pe.eaton.com

Photoelectric Sensor

11155AA17

UPC:782113056548

Dimensions:

- **Height:** .71 IN
- **Length:** 2.35 IN
- **Width:** .47 IN

Warranties:

- 3 year

Specifications:

- **Type:** Photoelectric Sensor
- **Cable Type:** PVC
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Polyurethane Foam (RIM)
- **Environmental Rating:** NEMA 1, 2, 3, 4, 4X, 6, 12, 13
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Power
- **Operating Mode:** Light
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Sensor Type:** Through Beam

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 11155AA17](#)

Certifications:

- cUL Recognized
- UL Recognized

Product compliance: No Data

