



Powering Business Worldwide

pe.eaton.com

General Purpose AC Rated Toggle Switches

7563K6

UPC:786685680743

Dimensions:

- **Height:** 1.2 IN
- **Length:** 1.312 IN
- **Width:** .75 IN

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125V, 10A at 250V
- **Bushing Length:** 0.469 in
- **Circuit Number:** D
- **Circuit Position Center:** OFF
- **Circuit Position Down:** ON
- **Horsepower:** 0.75 hp at 125-250V
- **Lever Length:** 0.563 in
- **Number Of Poles:** Two-pole
- **Terminals:** 0.250 in spade terminal
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 7563K6](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance:

- RoHS Compliant



