



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Industrial Control Transformer

**C0750E4CFB**

**UPC:**786680005350

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:**Epoxy encapsulated Laminations of high quality silicon steel to minimize core losses and optimize performance 50/60Hz operation 130°C insulation system standard Molded-in terminals for maximum durability

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Frequency Rating:** 60 Hz
- **Modification 1:** Primary fuse block for rejection type fuses
- **Primary Voltage:** 550/575/600V
- **Secondary Voltage:** 120/115/110V
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 750 VA

### Supporting documents:

- [Control Transformer Final Assembly - C0750E4CFB](#)
- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - C0750E4CFB](#)



**Certifications:**

- cUL Listed
- CSA Certified
- UL Listed

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.