



Powering Business Worldwide

pe.eaton.com

CLPT type current limiting fuse

5NCLPT-5E

UPC:782114610121

Dimensions:

- **Height:** X
- **Length:** 5.63 IN
- **Width:** X

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** NCLPT
- **Barrels:** Single barrel (non-indicating)
- **Diameter:** .81 IN
- **Interrupt Rating:** 63 kA
- **Amperage Rating:** 5E
- **Class:** E
- **Maximum Voltage:** 5.5 kV
- **Nominal Voltage:** 4.8 kV

Supporting documents:

- [Eatons Volume 14-Fuses](#)
- [Medium voltage power fuses](#)
- [Eaton Specification Sheet - 5NCLPT-5E](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

