



Powering Business Worldwide

pe.eaton.com

E57 Global Series Tubular Inductive Proximity Sensor

E57-18GS05-CDB

UPC:782114665084

Dimensions:

- **Height:** 2.99 IN
- **Length:** .71 IN
- **Width:** .71 IN

Weight:.1438 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 100 mA at 30 Vdc
- **Contact Configuration:** NPN Open Collector, Normally Open
- **Diameter:** .71 IN
- **Enclosure Material:** Nickel Plated Brass
- **Environmental Rating:** IP67, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Global Series inductive proximity sensors](#)
- [Eaton Specification Sheet - E57-18GS05-CDB](#)

Certifications: No Data



Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.