



Powering Business Worldwide

pe.eaton.com

Perfect Prox Photoelectric Sensor

E65-SMPP050-GL

UPC:782114389591

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Sensor will detect a 90% reflectance card at the Sensing Range; sensor will ignore a 90% reflectance card at the Cutoff Range

Warranties:

- 3 year

Specifications:

- **Type:** Back Ground Suppression
- **Contact Rating:** 200 mA at 18-264 Vac/18-50 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** AC: L1 switched, DC: NPN open collector
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Polycarbonate lens, PVC cable jacket, cycloloy body
- **Environmental Rating:** NEMA 1, 3, 4, 4X, 6, 6P, 12, 13, IP68, IP69K 2
- **Input Voltage:** 18-264 Vac 50/60 Hz, 18-50 Vdc
- **Led Indicators:** Power (green), output (red), TargetLock (orange)
- **Maximum Dc Current:** 200 mA
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** Auto reset S/C
- **Series:** E65



Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Test the Best Photoelectric Sensors: SM Series](#)
- [Eaton Specification Sheet - E65-SMPP050-GL](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance:

- CE Marked