



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Quicklag Industrial Thermal-Magnetic Circuit Breaker

**BAB3080HS**

**UPC:**786679509708

### Dimensions:

- **Height:** 3.5 IN
- **Length:** 4.1 IN
- **Width:** 3.6 IN

**Weight:**1.29 LB

**Notes:**HACR rated

### Warranties:

- 1 year

### Specifications:

- **Type:** Quicklag
- **Special Features:** 120V, 208V, 240V shunt trip
- **Amperage Rating:** 80A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Circuit Breaker Type:** BAB
- **Trip Type:** Non-Interchangeable
- **Mounting:** Bolt-on
- **Quantity:** 8

### Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB3080HS](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data



