



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E51 Series, Limit Switch Style, Modular Inductive Photoelectric Sensor

**E51NLP2**

**UPC:**782113129945

### Dimensions:

- **Height:** 4.89 IN
- **Length:** 1.54 IN
- **Width:** 1.82 IN

**Weight:**.975 LB

### Warranties:

- 3 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 600 mA
- **Contact Configuration:** Complementary NPN  
Open Collector
- **Enclosure Material:** Receptacle and Body: Die  
Cast Zinc, Head: Plastic
- **Environmental Rating:** NEMA  
3,3S,4,4X,6,6P,12,13, IP67
- **Input Voltage:** 10–30 Vdc
- **Led Indicators:** Lights when output is ON. One  
red LED for each output
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** -13° to 158°F (-25° to  
70°C)
- **Switch Type:** Photoelectric

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51NLP2](#)

### Certifications:

- CSA Certified
- UL Listed



**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.