



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Heavy-Duty Pushbutton Operator

10250T414L

UPC:782114554289

### Dimensions:

- Height: X
- Length: X
- Width: X

**Notes:** Unit does not include lamp. Order LED separately to match lens.

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Bezel:** Chrome
- **Illumination:** Illuminated
- **Led Lamp Number:** Bayonet base
- **Light Unit Type:** LED, transformer
- **Light Unit Voltage:** 480 Vac
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T414L](#)

### Certifications:

- CSA Certified
- UL Listed

### Product compliance:

- CE Marked



