



Powering Business Worldwide

pe.eaton.com

General-Purpose Encapsulated Transformer

S10N11E25N

UPC:786680108495

Dimensions:

- **Height:** 23.31 IN
- **Length:** 14.12 IN
- **Width:** 16.35 IN

Weight:371 LB

Notes:Model N

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Electrostatically shielded
- **Type:** General-Purpose Encapsulated Transformer
- **Design:** EP
- **Coil Material:** Aluminum windings
- **Enclosure:** NEMA 3R
- **Frame:** 182
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 120 X 240V
- **Secondary Voltage:** 120/240V
- **Tap Size:** NONE
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 25 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 90B

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)



- [Eaton Specification Sheet - S10N11E25N](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.