



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CN35 or A202 Enclosed Lighting Contactor

**ECL03C1B2A**

**UPC:**782114039441

### Dimensions:

- **Height:** 9.51 IN
- **Length:** 5.62 IN
- **Width:** 5.71 IN

**Weight:**5.2 LB

**Notes:** Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 30A
- **Coil Voltage:** 220V/50 Hz, 240V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 45 mm
- **Number Of Poles:** Two-pole
- **Type:** Non-combination electrically held

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECL03C1B2A](#)

### Certifications:

- UL Listed
- cUL Listed

**Product compliance:** No Data



