



Powering Business Worldwide

pe.eaton.com

Photoelectric Sensor

14150RL17

UPC:782113011271

Dimensions:

- **Height:** .71 IN
- **Length:** 2.75 IN
- **Width:** .47 IN

Warranties:

- 3 year

Specifications:

- **Type:** Photoelectric Sensor
- **Contact Rating:** 80 mA AC/100 mA DC at 20-132V
- **Cable Type:** PVC
- **Contact Configuration:** Isolated SSR
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Polyurethane Foam (RIM)
- **Environmental Rating:** NEMA 1, 2, 3, 4, 4X, 6, 12, 13
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Maximum Ac Current:** 80 mA
- **Maximum Dc Current:** 100 mA
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** Protected for loads < 32 Vac or 2 Vdc
- **Sensor Type:** Retroreflective

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 14150RL17](#)

Certifications:

- UL Recognized
- cUL Recognized



Product compliance: No Data

© 2016 Eaton. All rights reserved.