



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Power-Suppress T7

05146002-5501

UPC:790341030711

### Dimensions:

- **Height:** 3.5 IN
- **Length:** 19.4 IN
- **Width:** 17 IN

**Weight:**34 LB

**Notes:**Startup with UPS batteries in absence of utility power

### Warranties:

- 2 year limited factory

### Specifications:

- **Type:** Noise suppressor
- **Battery Type:** VRLA
- **Frequency Rating:** 45-65 Hz
- **Humidity:** 5-90% non-condensing
- **Input:** (1) 5-15P
- **Operating Temperature:** 0° to 40°C (25°C recommended)
- **Output:** (6) 5-15R
- **Topology:** Online double conversion
- **User Interface:** Front panel on, off, test/alarm, bypass modes and alarm indicator lights, bar graph indicator light
- **Volt Ampere Rating:** 1000 KVA
- **Cable Type:** Communication cable, 5-20P power cord
- **Color:** Beige
- **Cord Length:** 864 IN
- **Runtime:** 5 min full load, 14 min half load
- **Wattage:** 700W
- **Battery Rating:** (2) Internal 12V, 9 Ah
- **Communication:** RS-232 serial
- **Configuration:** Rackmount/tower



- **Indicator:** Bar graph (LED), alarm indicator lights (LED)
- **Software:** Fail-Safe III, LanSafe III Power Management Software

**Supporting documents:**

- [Eaton Specification Sheet - 05146002-5501](#)

**Certifications:**

- UL 497A
- NOM-019-SCFI
- VCCI
- CSA Certified
- cULus Listed
- ICES-003
- UL 1778
- CSA Std. C22.2
- NOM

**Product compliance:**

- FCC Part 15