



Powering Business Worldwide

pe.eaton.com

Type C361 Flange Mounted Disconnect Switch

C361NF1

UPC:782113566160

Dimensions:

- **Height:** 10.438 IN
- **Length:** 25.344 IN
- **Width:** 17.813 IN

Notes:Maximum horsepower ratings refer to switch only

Warranties:

- 1 year

Specifications:

- **Type:** Switch and operating mechanism with handle
- **Amperage Rating:** 200A
- **Depth Range:** 7-16 in
- **Enclosure:** NEMA 1 or 12
- **Fuse Clip Rating:** Non-fusible
- **Handle Length:** 4 IN
- **Max Hp Rating:** 40 hp at 208 Vac, 60 hp at 240 Vac, 125 hp at 480 Vac, 150 hp at 600 Vac, 40 hp at 250 Vdc
- **Mounting:** Right-hand
- **Wire Size:** #250-6 AWG Cu/Al

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - C361NF1](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



