



Powering Business Worldwide

pe.eaton.com

E50 Heavy Duty Factory Sealed 6P+ Limit Switch

E50SBL6PC

UPC:782113728186

Dimensions:

- **Height:** 3.58 IN
- **Length:** 1.54 IN
- **Width:** 1.58 IN

Weight:.8688 LB

Notes:Switch body only; full switch requires a switch body and operating head.

Warranties:

- 1 year

Specifications:

- **Connection:** 9 Pin Mini Connector
- **Contact Rating:** 10A at 240Vac, 1A at 125Vdc
- **Contact Configuration:** 2NO-2NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** -40° to 250°F (-40° to 121°C)

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50SBL6PC](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance:

- CE Marked



