



Powering Business Worldwide

pe.eaton.com

CE Marked Control Transformer

CE0500K3ZCEFS

UPC:786680042065

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:Epoxy resin impregnated coil design, 50/60 Hz operation, 180°C insulation system

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTK
- **Modification 1:** Factory-mounted finger-safe terminal shields
- **Primary Voltage:** 380/415/480V
- **Secondary Voltage:** 115V at 250 VA, 24V at 210 VA, 24V at 40 VA
- **Tap Size:** None
- **Temperature Rating:** 115°C
- **Type:** CE Marked Control Transformer
- **Volt Ampere Rating:** 500 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - CE0500K3ZCEFS](#)

Certifications:

- CSA Certified
- IEC 61558-2
- UL Listed



- cUL Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.