



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Continuous Duty AC Solenoid

10370H392

UPC:782113236261

### Dimensions:

- **Height:** 6.13 IN
- **Length:** 3.75 IN
- **Width:** 3.88 IN

**Notes:** Mounting of solenoids “with conduit box”—Size A are for wall mounting—Size B, C and D are for floor mounting.

### Warranties:

- 1 year

### Specifications:

- **Magnetic Force Against Gravity:** 11.15 lbs at 100% voltage, 8.75 lbs at 85% voltage
- **Magnetic Force Horizontal:** 12.4 lbs at 100% voltage, 10 lbs at 85% voltage
- **Magnetic Force With Gravity:** 13.65 lbs at 100% voltage, 11.25 lbs at 85% voltage
- **Frequency Rating:** 60 Hz
- **Full Load Current Range:** Inrush 18A/Sealed 1.58A
- **Mounting:** Floor mount
- **Operation:** Push type
- **Size:** D
- **Special Features:** With conduit box
- **Voltage Rating:** 110V

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - 10370H392](#)

**Certifications:** No Data

**Product compliance:** No Data



