



Powering Business Worldwide

pe.eaton.com

CLPT current limiting fuse disconnect mounting parts

15CLPT-GNM-A

UPC:786670254270

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** 1.625 IN

Notes: Includes live parts. End fittings supplied only when required.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CLPT
- **Impulse Withstand Voltage:** 95A
- **Maximum Voltage:** 15.5 kV
- **Mounting:** Non-disconnect
- **Amperage Rating:** 150A
- **Insulator Type:** Glass polyester
- **Prod Size:** 1-5/8 inch 0.53E-1.5E single barrel
- **Used With:** Type CLPT current limiting fuses

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Medium voltage power fuses](#)
- [Eaton Specification Sheet - 15CLPT-GNM-A](#)

Certifications: No Data

Product compliance: No Data

