



Powering Business Worldwide

pe.eaton.com

30.5 mm, Class I Division 2 Pushbutton Operator

10250T476H

UPC:782114510827

Dimensions:

- Height: X
- Length: X
- Width: X

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Class I Division 2
- **Bezel:** Chrome
- **Illumination:** Illuminated
- **Led Lamp Number:** #757
- **Light Unit Type:** Incandescent, full voltage
- **Light Unit Voltage:** 24 Vac/dc
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T476H](#)

Certifications:

- CSA Certified
- UL 505

Product compliance:

- CE Marked



