



Powering Business Worldwide

pe.eaton.com

Enclosed Rotary Disconnect Switch

DR3100UW

UPC:782114872901

Dimensions:

- **Height:** 7.3 IN
- **Length:** 15.5 IN
- **Width:** 11 IN

Weight:11 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Enclosed Rotary
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 4X
- **Enclosure Material:** Stainless steel
- **Fuse Configuration:** Non-fusible
- **Max Hp Rating:** 20 at 240 Vac, 40 at 480 Vac, 60 at 600 Vac
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Enclosed Rotary Disconnect Switch
- **Voltage Rating:** 600V

Supporting documents:

- [Eaton Specification Sheet - DR3100UW](#)

Certifications:

- UL Listed

Product compliance: No Data



