



Powering Business Worldwide

pe.eaton.com

Industrial Control Transformer

F10005

UPC:786680004292

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Weight:150 LB

Notes:Resin encapsulated, 60 Hz operation, 180°C insulation system, Convenient screw-type terminal board

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** AP
- **Frame:** 258
- **Modification 1:** Side/wall mounted
- **Primary Voltage:** 240 X 480V
- **Secondary Voltage:** 120/240V
- **Special Features:** Electrostatically Shielded
- **Tap Size:** 2 at +2.5% FCAN, 2 at -2.5% FCBN
- **Temperature Rating:** 115°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 10000 VA
- **Wiring Connection:** 400A

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - F10005](#)

Certifications:



- UL Recognized

Product compliance: No Data

© 2016 Eaton. All rights reserved.