



Powering Business Worldwide

pe.eaton.com

FERRUPS UPS

FD000BB3A0A0A0A

UPC:790341042127

Dimensions:

- **Height:** 15.1 IN
- **Length:** 20.2 IN
- **Width:** 15.2 IN

Weight:102 LB

Warranties:

- 2 year

Specifications:

- **Battery Type:** Internal sealed/gas recombinant/lead-acid battery
- **Efficiency:** 88% efficiency
- **Frequency Rating:** 60 Hz
- **Humidity:** 5 to 95% non-condensing
- **Input:** (1) 5-15P
- **Operating Temperature:** 0° to 40°C
- **Output:** (6) 5-15R
- **Topology:** Ferroresonant
- **User Interface:** On/off switch, alarm switch, 5 front indicator lights
- **Volt Ampere Rating:** 1150 KVA

Supporting documents:

- [Eaton FERRUPS UPS](#)
- [Product and Service Catalog](#)
- [Eaton Specification Sheet - FD000BB3A0A0A0A](#)

Certifications:

- FCC Cat. A
- ANSI/IEEE Std C62.45
- EN 62040-2
- ANSI/IEEE Std C62.41
- UL Listed



- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.