



Powering Business Worldwide

pe.eaton.com

CE Marked Control Transformer

CE0500E1BCE

UPC:786680041853

Dimensions:

- **Height:** 4.764 IN
- **Length:** 5.512 IN
- **Width:** 5.236 IN

Weight:19.2 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals, Non-short circuit-proof

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Primary Voltage:** 120 X 240V
- **Secondary Voltage:** 24V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** CE Marked Control Transformer
- **Volt Ampere Rating:** 500 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - CE0500E1BCE](#)

Certifications:

- UL Listed
- IEC 61558-2



- CSA Certified
- cUL Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.