



Powering Business Worldwide

pe.eaton.com

Perfect Prox Photoelectric Sensor

13104A6515

UPC:782114290545

Dimensions:

- **Height:** .71 IN
- **Length:** 2.6 IN
- **Width:** .47 IN

Warranties:

- 3 year

Specifications:

- **Type:** Perfect Prox Photoelectric Sensor
- **Contact Rating:** 300 mA AC/DC at 90-132 Vac/18-50 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire AC/DC
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Polyurethane Foam (RIM)
- **Environmental Rating:** NEMA 1, 3, 4, 4X, 6, 12, 13, IP69k
- **Input Voltage:** 90-132 Vac 50/60 Hz, 18-50 Vdc
- **Led Indicators:** Output ON
- **Maximum Ac Current:** 300 mA
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Auto reset
- **Sensor Type:** Back Ground Suppression

Supporting documents:

- [Comet series - Photoelectric sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 13104A6515](#)

Certifications:

- UL Recognized



- cUL Recognized

Product compliance: No Data

© 2016 Eaton. All rights reserved.