



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E50 Heavy Duty Plug-In Limit Switch

**E50AW1Y1**

**UPC:**782114426654

### Dimensions:

- **Height:** 4.93 IN
- **Length:** 1.54 IN
- **Width:** 1.78 IN

**Weight:**1.1063 LB

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 240Vac, 1A at 250Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 250°F (-10° to 121°C)
- **Switch Type:** Wobble Stick

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50AW1Y1](#)

**Certifications:** No Data

**Product compliance:** No Data

